

## S-SFM Spray Filling machine



**Usage:** This machine is mainly suitable for Filling Spray 5-500ML, adding spray heads and sealing on plastic and glass bottle, and it is applied to pharmaceutical, daily chemicals, adopt piston pump to filling, and vibrating together with pneumatic to feeding Caps, then to on sealing. this machine could used in combination line with another machine, protection cover could be optional

### Machine features:

1. This machine adopts constant torque screw caps, equipped with automatic sliding device, to prevent the cap damage.
2. Peristaltic pump filling, measuring precision, convenient manipulation.
3. Filling system has function of suck back, avoid liquid leak through.
4. Color touch screen display, PLC control system, no bottle no filling, no adding plug, no capping.
5. Adding plug device can choose fixed mold or mechanical vacuum mold.
6. Machine body is made by 304 stainless steel, easy to dismantle and clean, full compliance with GMP requirements.

### Technical parameter:

Scope	5-500ml
Capacity	30-50 bottles/min
Air Wastage	1m <sup>3</sup> /h 0.3-0.4kg/m <sup>2</sup>
Filling volume	10-50ml
Filling head	4
Pass rate	≥ 98%
Power supply	380V or 220V, 50/60Hz
Power	2.8 KW
Overall dimension	2100 × 1350 × 1730mm
Net weight	650kg